

# STYLEA

5923XOI065B10-11X20/10D23 9011/9011

EAN 4031582343588  
Order number 00079444



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor with intermittend brake
Load capacity at 1.8 mph	110.23 lb
Electric conductive	✓
Load capacity Static	220.46 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.68 in
Overall width	1.69 in
Overall weight	0.28 lb

## WHEEL

Body material	Polyamide, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	0.31 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.31 in
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Color	Graphite black (RAL9011)
Offset	0.98 in
Swivel radius	2.09 in
Swivel interference	4.17 in
Dome diameter	0.91 in

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in
Stem length	0.79 in

PRODUCT INFORMATION

# STYLEA

5923XOI065B10-11X20/10D23 9011/9011

EAN 4031582343588  
Order number 00079444



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

