

AGILA

267FPOO4X1.25P30-13

EAN 4031582435337



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Castor with butterfly wheel brake
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	150 kg
Load capacity Static	350 kg
Overall height	127 mm

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	101.6 mm
Tread width	31.75 mm
Axle hole diameter	10 mm
Hardness of tread (D)	66 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	88.8 mm
Swivel interference	176 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm
Hint	Castors can be mounted with standard screws of any length.