

# LINEA LOW HEIGHT

5940UAP100P30-8 LH RAL7001

EAN 4031582373035

Broj porudžbine 00079778



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●●●

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●●○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Linea low height
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	40 °C
Sveukupna visina	103 mm
Ukupna širina	73 mm
Ukupna težina	0,249 kg

## TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
štitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	20 mm
Teškoća gazećeg omotac (A)	92 Šor A

## KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	precizini kuglicni lezaj
Boja	Srebrna siva (RAL7001)
ofset	32 mm
okretni radijus	88 mm
Otpor okretanju	180 mm
Prečnik kupole	41 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	8 mm

Deutscher  
dizajner  
ClubInterzum  
nagradaIF nagrada za  
Dizajn

# LINEA LOW HEIGHT

5940UAP100P30-8 LH RAL7001

EAN 4031582373035  
Broj porudžbine 00079778



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

