

MAXTECH

UAD125X40-Ø20 HL58

EAN 4031582452853



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (D)	60 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.507 kg

MAXTECH

UAD125X40-Ø20 HL58

EAN 4031582452853



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

