

AGILA

2478PJP075P60-67X60

EAN 4031582302400
Order number 00004810



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall width	1.69 in
Overall weight	0.44 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Color	Blue passivated
Dome diameter	1.69 in

FITTING

Fitting type	Rectangular plate
Plate length	2.64 in
Plate width	2.36 in
Plate hole length (Minimum)	1.57 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.57 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

AGILA

2478PJP075P60-67X60

EAN 4031582302400
Order number 00004810



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

