

ELASTECH

UFC125X40@08X45

EAN 4031582422290



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.502 kg

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (A)	64 Shore A

HOUSING

Stainless	✓
-----------	---

ELASTECH

UFC125X40@08X45

EAN 4031582422290



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

