

NOVATECH

ETP075X50-Ø25 HL50

EAN 4031582340136



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	75 mm
Širina omotac	50 mm
dimenzija rupa osovina	25 mm
dužina glavcine	50 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip ležaja	6005

PERFORMANSE

Performanse kotrljanja ● ● ● ● ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip Tocak

Nosivost na 3 km/h 550 kg

Statički Nosivost 1100 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

TEHNIČKI CRTEŽI

