

PRODUCT INFORMATION

SUPRATECH

PJR160x46-Ø25 TFR

EAN 4031582392609



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.54 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Axle Hole Diameter	25 mm
Hub Length	58 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJR160x46-Ø25 TFR

EAN 4031582392609



BETTER MOBILITY. BETTER LIFE.

Product Drawings

