

NOVATECH

ITP 160x50-Ø25 HL60 soft cv

EAN 4031582332179



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Tread profile	convex
Tread hardness	soft
Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Traffic gray A (RAL7042)
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1212.54 lb
Load capacity at 3.7 mph	970.03 lb
Electric conductive	no
Stainless	no
Load capacity Static	2425.08 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	2.58 lb




PRODUCT INFORMATION

NOVATECH

ITP 160x50-Ø25-H160-soft cv

EAN 4031582332179

Order number 00839136



BETTER MOBILITY. BETTER LIFE.