


FOOTMASTER

FOOT MASTER GASD-150-ASF-HUD

EAN 4031582495225



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	○ ○ ○ ○ ○
Buka u pokretu	○ ○ ○ ○ ○
Ishrana	○ ○ ○ ○ ○
otpornost na rdju	○ ○ ○ ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Footmaster
Tip	Okretanje Tocak
Nosivost na 3 km/h	630 kg
Električni provod	no
nerdjajuci	no
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	90 °C
Sveukupna visina	200 mm
Ukupna širina	160 mm
Ukupna težina	17.54 kg

KUCISTE

ofset	37 mm
okretni radijus	122 mm
Otpor okretanju	244 mm
Prečnik kupole	145 mm

TOCAK

Nošenje	Nemašinsko glavcina
Prečnik	150 mm
Širina omotac	40 mm
Širina tela	40 mm

PRILAGOĐAVANJE

Dužina ploče	145 mm
Širina ploče	145 mm
Dužina otvora ploče (maksimalna)	120 mm
Širina otvora ploče (maksimalna)	120 mm
Prečnik otvora ploče	11 mm

FOOTMASTER

FOOT MASTER GASD-150-ASF-HUD

EAN 4031582495225

Broj porudžbine 00800107
Product Drawings



BETTER MOBILITY. BETTER LIFE.

