

BASETECH

POO100X36-Ø12 WHITE

EAN 4031582410358



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	36 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Teškoća gazećeg omotac (D)	65 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Basetech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	160 kg
Statički Nosivost	320 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,105 kg

BASETECH

POO100X36-Ø12 WHITE

EAN 4031582410358



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

