

# NOVATECH

ETP 075X62-Ø20 HL62

EAN 4031582318494  
Order number 00806197



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	2.95 in
Tread width	2.44 in
Axle hole diameter	0.79 in
Hub length	2.44 in
Body width	2.44 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6204

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1212.54 lb
Load capacity at 3.7 mph	970.03 lb
Load capacity Static	2425.08 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	1.82 lb

# NOVATECH

ETP 075X62-Ø20 HL62

EAN 4031582318494  
Order number 00806197



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

