

# LEVINA

5370PJP125P30-11 2.0 7001

EAN 4031582324594  
Order number 00066198



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |       |
|----------------------|-------|
| Roll performance     | ●●●○○ |
| Movement noise       | ●●●●● |
| Attrition            | ●●●○○ |
| Corrosion resistance | ●●●●● |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Levina                    |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 220.46 lb                 |
| Load capacity Static        | 440.92 lb                 |
| Temperature range (Minimum) | 14 °F                     |
| Temperature range (Maximum) | 104 °F                    |
| Overall height              | 6.34 in                   |
| Overall width               | 2.32 in                   |
| Overall weight              | 1.17 lb                   |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Wheel color           | Silver gray (RAL7001)  |
| Threadguards          | With threadguard       |
| Diameter              | 4.92 in                |
| Tread width           | 1.26 in                |
| Body width            | 1.26 in                |
| Hardness of tread (A) | 83 Shore A             |

## HOUSING

|                     |                       |
|---------------------|-----------------------|
| Material            | Polyamide             |
| Fork shape          | Slim                  |
| Swivel bearing      | Two ball races        |
| Color               | Silver gray (RAL7001) |
| Offset              | 1.5 in                |
| Swivel radius       | 3.96 in               |
| Swivel interference | 7.91 in               |
| Dome diameter       | 2.32 in               |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 0.43 in   |



Universal  
Design  
Award



Deutscher  
Designer  
Club

# LEVINA



5370PJP125P30-11 2.0 7001

EAN 4031582324594  
Order number 00066198



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Universal  
Design  
Award



Deutscher  
Designer  
Club