PRODUCT INFORMATION

ELASTECH

UFR 100x34-Ø12 HL44,4 tyre-5015

EAN 4031582070392



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Elastech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.25 kg

WHEEL

Tread hardness	soft
Body material	Polyamide
Tread Material Mix	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	34 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Body width	34 mm
Hardness of tread (A)	63 Shore A

© Copyright 2026 TENTE International GmbH


ELASTECH

UFR 100x34-Ø12 HL44,4 tyre-5015

EAN 4031582070392

Order number 00030733

Product Drawings



© Copyright 2026 TENTE International GmbH