

DURATECH

TOP 065X32-Ø12 HL32

EAN 4031582332315
Order number 00829018



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	65 mm
Tread width	32 mm
Axle hole diameter	12 mm
Hub length	32 mm
Body width	32 mm
Hardness of tread (D)	75 Shore D
Bearing type	6201

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	290 kg
Load capacity at 6 km/h	240 kg
Load capacity Static	480 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.169 kg

DURATECH

TOP 065X32-Ø12 HL32

EAN 4031582332315
Order number 00829018



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

