PRODUCT INFORMATION

MAXTECH

XSP150x32-Ø8 LN48 TFR

EAN 4031582391213



Image may differ from the original product

WHEEL

Body material	Polyamide, electric conductive
Tread Material Mix	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Axle Hole Diameter	8 mm
Hub Length	36 mm
Hardness of tread (D)	40 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	300 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.44 kg

© Copyright 2026 TENTE International GmbH


MAXTECH

XSP150x32-Ø8 LN48 TFR

EAN 4031582391213

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH