

PRODUCT INFORMATION

BASETECH

POR080x34-Ø12 white

EAN 4031582410372



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Basetech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 125 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 250 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.1 kg                        |



BETTER MOBILITY. BETTER LIFE.

WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread Material Mix    | Identical with wheel body |
| Bearing               | Roller bearing            |
| Threadguards          | Without threadguard       |
| Diameter              | 80 mm                     |
| Tread width           | 34 mm                     |
| Axle Hole Diameter    | 12 mm                     |
| Hub Length            | 44.4 mm                   |
| Hardness of tread (D) | 65 Shore D                |

# BASETECH

POR080x34-Ø12 white

EAN 4031582410372



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

