

# BASETECH

POR 100X36-Ø12 HL44,4

EAN 4031582320770  
Order number 00030952



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Identical with wheel body |
| Bearing               | Roller bearing            |
| Wheel color           | Graphite black (RAL9011)  |
| Threadguards          | Without threadguard       |
| Diameter              | 3.94 in                   |
| Tread width           | 1.42 in                   |
| Axle hole diameter    | 0.47 in                   |
| Hub length            | 1.75 in                   |
| Body width            | 1.42 in                   |
| Hardness of tread (D) | 65 Shore D                |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Basetech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 352.74 lb                     |
| Load capacity Static        | 705.48 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 0.32 lb                       |

# BASETECH

POR 100X36-Ø12 HL44,4

EAN 4031582320770  
Order number 00030952



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

