

STORA

2370PIP100S74

EAN 4031582369359



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Stora |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 80 kg |
| Load capacity Static | 160 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 128 mm |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread hardness | soft |
| Tread material | Solid rubber, non-marking |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Hardness of tread (A) | 75 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Slim |
| Swivel bearing | Two ball races |
| Offset | 35 mm |
| Swivel radius | 85 mm |
| Swivel interference | 170 mm |

FITTING

| | |
|--------------|---|
| Fitting type | Threaded stem with hexagon neck, top, riveted |
|--------------|---|