PRODUCT INFORMATION

MONO

5025PJH080S70-10X15 TFR

EAN 4031582385762



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Mono
Type	Swivel caster with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	154.32 lb
Electric conductive	no
Stainless	no
Load capacity Static	308.65 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.33 in
Overall weight	0.44 lb

HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel bearing	Stem, swiveling
Offset	1.34 in
Swivel radius	2.91 in
Swivel interference	5.83 in
Thread diameter	0 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	3.15 in
Tread width	0.94 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	0.39 in
Stem length	0.59 in

© Copyright 2026 TENTE International GmbH


MONO

5025PJH080S70-10X15 TFR

EAN 4031582385762

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH