

STORA

2875ZIP125S74 DROITE TFR

EAN 4031582386561



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	153 mm
Overall weight	0.927 kg

WHEEL

Body material	Flanged wheel
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Special Function
Swivel bearing	Two ball races
Offset	43 mm
Swivel radius	105.5 mm
Swivel interference	211 mm
Thread diameter	0 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top, riveted
Stem length	15.5 mm

ADDITIONAL INFORMATION

Designed for the following palletsize: track width: approx. 2,75 mm, groove width: approx. 5,7 mm, groove depth: > 10 mm.

PRODUCT INFORMATION

STORA

2875ZIP125S74 DROITE TFR

EAN 4031582386561



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

