

PRODUCT INFORMATION

NOVATECH

ETP080x30-Ø12 HL28\_TBE

EAN 4031582438055



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |          |
|-----------------------------|----------|
| Product Name                | Novatech |
| Type                        | Wheel    |
| Load capacity at 3 km/h     | 180 kg   |
| Electric Conductive         | No       |
| Stainless                   | No       |
| Temperature range (Minimum) | -20 °C   |
| Temperature range (Maximum) | 60 °C    |
| Overall weight              | 0.5 kg   |

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Steel, iron            |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 80 mm                  |
| Tread width           | 30 mm                  |
| Axle Hole Diameter    | 12 mm                  |
| Hub Length            | 28 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Bearing type          | 6201                   |

