PRODUCT INFORMATION

ICS

5328PJP100P50 7001

EAN 4031582030549



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●●○
Attrition	●●●○○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	ICS
Type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	141 mm
Overall width	52 mm
Overall weight	0.5 kg

HOUSING

Housing Material	Polyamide
Fork shape	Slim
Housing Color	Silver grey (RAL7001)
Dome diameter	52 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel Color	Silver grey (RAL7001)
Threadguards	Integrated threadguard
Diameter	100 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm

IF Design Award

© Copyright 2026 TENTE International GmbH


ICS


5328PJP100P50 7001

EAN 4031582030549

BETTER MOBILITY. BETTER LIFE.

Product Drawings





IF Design Award

© Copyright 2026 TENTE International GmbH