

DELTA TWIN

9940ITP125P63

EAN 4031582365641
Order number 00837782



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Delta twin
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1653.47 lb
Load capacity at 3.7 mph	1322.77 lb
Load capacity Static	3306.93 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	7.01 in
Overall width	6.18 in
Overall weight	10.34 lb

WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Color	Transparent coating
Offset	2.17 in
Swivel radius	4.98 in
Swivel interference	9.96 in
Dome diameter	5.35 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	4.13 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

DELTA TWIN

9940ITP125P63

EAN 4031582365641
Order number 00837782



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

