PRODUCT INFORMATION

# ALPHA STAINLESS

8478PID125P62

EAN 4031582381702



Image may differ from the original product

## PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●●● |

## CORE ATTRIBUTES

| | |
|---|---|
| Product name | Alpha stainless |
| Type | Fixed caster |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 220.46 lb |
| Electric conductive | no |
| Stainless | Yes |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 6.1 in |
| Overall width | 3.35 in |
| Overall weight | 1.82 lb |

## HOUSING

| | |
|---|---|
| Housing Material | Stainless steel, heavy |
| Fork shape | Broad |
| Housing Color | Stainless steel |

## WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Roller bearing, stainless |
| Axle | Screwed with nut |
| Wheel color | Graphite black (RAL9011) |
| Diameter | 4.92 in |
| Tread width | 1.46 in |
| Body width | 1.46 in |
| Hardness of tread (A) | 80 Shore A |

## FITTING

| | |
|---|---|
| Fitting type | Rectangular plate |
| Plate length | 3.94 in |
| Plate width | 3.35 in |
| Plate hole length (Minimum) | 3.03 in |
| Plate hole length (Maximum) | 2.36 in |
| Plate hole width (Minimum) | 3.03 in |
| Plate hole width (Maximum) | 3.15 in |
| Plate hole diameter | 0.35 in |

© Copyright 2026 TENTE International GmbH


# ALPHA STAINLESS


8478PID125P62

EAN 4031582381702

Order number 00035730

**Product Drawings**




© Copyright 2026 TENTE International GmbH