

ELASTECH

JFC125X32-Ø8

EAN 4031582319941
Broj porudžbine 00024549

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip kućišta	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	150 kg
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,679 kg

TOCAK

Materijal za telo	Cink die-cast
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	precizini kuglicni lezaj, nerdjajuci
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	32 mm
dimenzija rupa osovina	8 mm
duzina glavcine	35,5 mm
Teškoća gazećeg omotac (A)	75 Šor A

ELASTECH

JFC125X32-Ø8

EAN 4031582319941
Broj porudžbine 00024549



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

