

PRODUCT INFORMATION

# NOVATECH

ETY080x20-Ø20 HL14

EAN 4031582419047



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing (RS/2RS)
Diameter	80 mm
Tread width	20 mm
Axle Hole Diameter	20 mm
Hub Length	14 mm
Hardness of tread (A)	92 Shore A

## PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

## CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	140 kg
Electric Conductive	No
Stainless	No
Load capacity Static	280 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.3 kg

# NOVATECH

ETY080x20-Ø20 HL14

EAN 4031582419047



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

