

DURATECH

UOR150X46-Ø20 HL58

EAN 4031582496680
Broj porudžbine 10000776

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	46 mm
dimenzija rupa osovine	20 mm
dužina glavčine	58 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	500 kg
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,57 kg

DURATECH

UOR150X46-Ø20 HL58

EAN 4031582496680
Broj porudžbine 10000776



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

