

PRODUCT INFORMATION

BASETECH

POO3.5x1.25-Ø0.5 HL 40

EAN 4031582436099



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	88.9 mm
Tread width	31.75 mm
Axle Hole Diameter	12.1 mm
Hub Length	40 mm
Hardness of tread (D)	66 Shore D

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Basetech
Type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	125 kg
Electric Conductive	No
Stainless	No
Load capacity Static	250 kg

BASETECH

POO3.5x1.25-Ø0.5 HL 40

EAN 4031582436099



BETTER MOBILITY. BETTER LIFE.

Product Drawings

