

# COMPACTA

1430PII036P40-42

EAN 4031582332551



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	30 kg
Load capacity Static	60 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	40 °C
Overall height	48 mm
Overall weight	0.07 kg

## WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Solid rubber, non-marking
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	36 mm
Tread width	15 mm
Hardness of tread (A)	75 Shore A

## HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Offset	13 mm
Swivel radius	32 mm
Swivel interference	64 mm

## FITTING

Fitting type	Square plate
Plate length	42 mm
Plate width	42 mm
Plate hole length (Maximum)	35 mm
Plate hole width (Maximum)	35 mm
Plate hole diameter	5.5 mm

# COMPACTA

1430PII036P40-42

EAN 4031582332551



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

