

# GALEA

5070PJP125P60-90X70

EAN 4031582308846  
Order number 00071816



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Galea                     |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall height              | 163 mm                    |
| Overall weight              | 0.415 kg                  |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polypropylene          |
| Tread material        | Thermoplastic rubber   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 125 mm                 |
| Tread width           | 30 mm                  |
| Hardness of tread (A) | 87 Shore A             |

## HOUSING

|                     |                |
|---------------------|----------------|
| Material fork       | Polyamide      |
| Fork shape          | Closed         |
| Swivel bearing      | Two ball races |
| Offset              | 40 mm          |
| Swivel radius       | 102.5 mm       |
| Swivel interference | 205 mm         |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 90 mm             |
| Plate width                 | 70 mm             |
| Plate hole length (Minimum) | 60 mm             |
| Plate hole length (Maximum) | 70 mm             |
| Plate hole width (Minimum)  | 50 mm             |
| Plate hole width (Maximum)  | 55 mm             |
| Plate hole diameter         | 8 mm              |

PRODUCT INFORMATION

# GALEA

5070PJP125P60-90X70

EAN 4031582308846  
Order number 00071816



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

