

PRODUCT INFORMATION

DURATECH

TOP 080x74-Ø20 HL80

EAN 4031582331028



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1543.23 lb
Load capacity at 3.7 mph	1234.59 lb
Electric conductive	no
Stainless	no
Load capacity Static	3086.47 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.99 lb



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	2.91 in
Axle hole diameter	0.79 in
Hub length	3.15 in
Body width	2.91 in
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

DURATECH

TOP 080x74-Ø20 HL80

EAN 4031582331028

Order number 00829536
Product Drawings



BETTER MOBILITY. BETTER LIFE.

