PRODUCT INFORMATION

MAXTECH

UAD 125x38-Ø12 HL44 natural/3004

EAN 4031582322774



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Wheel color	Natural white
Diameter	4.92 in
Tread width	1.5 in
Axle hole diameter	0.47 in
Hub length	1.73 in
Body width	1.5 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●●●

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	0.82 lb

© Copyright 2026 TENTE International GmbH


MAXTECH

UAD 125x38-Ø12 HL44 natural/3004

EAN 4031582322774

Order number 00034192

Product Drawings



© Copyright 2026 TENTE International GmbH