

GALEA

5070PJH100P60-90X70 7035/7042/7035/7035

EAN 4031582308594



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement noise	● ● ● ● ○ ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ● ●

CORE ATTRIBUTES

Product name	Galea
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.47 in
Overall width	2.56 in
Overall weight	0.96 lb

HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races
Housing Color	Light gray (RAL7035)
Offset	1.57 in
Swivel radius	3.54 in
Swivel interference	7.09 in
Dome diameter	2.32 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Tread color	Traffic gray A (RAL7042)
Wheel color	Traffic gray A (RAL7042)
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.18 in
Axle hole diameter	0 in
Hub length	0 in
Body width	1.18 in
Hardness of tread (A)	90 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	3.54 in
Plate width	2.76 in
Plate hole length (Minimum)	1.97 in
Plate hole length (Maximum)	2.14 in
Plate hole width (Minimum)	2.36 in
Plate hole width (Maximum)	2.76 in
Plate hole diameter	0.32 in

GALEA

5070PJH100P60-90X70 7035/7042/7035/7035

EAN 4031582308594

Order number 00071776

Product Drawings



BETTER MOBILITY. BETTER LIFE.

