PRODUCT INFORMATION

AGILA CARE

2474PJO100R26-28S45

EAN 4031582301564



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila care
Type	Swivel caster with central, total or directional lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Electric conductive	no
Stainless	no
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.43 in
Overall weight	1.76 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	1.5 in
Swivel radius	3.46 in
Swivel interference	6.93 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Stem with cam hole for profile bars
Bolt diameter	1.1 in
Bolt length	3.78 in

© Copyright 2026 TENTE International GmbH


AGILA CARE

2474PJO100R26-28S45

EAN 4031582301564

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH