

# COMPACTA

1430POI025P60-35X30

EAN 4031582336658  
Order number 00032081



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	10 kg
Load capacity Static	20 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	36 mm
Overall width	24 mm
Overall weight	0.03 kg

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	25 mm
Tread width	12 mm
Body width	12 mm
Hardness of tread (D)	65 Shore D

## HOUSING

Material fork	Steel sheet, light
Fork shape	Broad
Swivel bearing	One ball race
Colour	Blue passivated
Offset	9 mm
Swivel radius	21.5 mm
Swivel interference	43 mm
Dome diameter	24.5 mm

## FITTING

Fitting type	Rectangular plate
Plate length	35 mm
Plate width	30 mm
Plate hole length (Maximum)	23 mm
Plate hole width (Maximum)	28 mm
Plate hole diameter	4.2 mm

# COMPACTA

1430POI025P60-35X30

EAN 4031582336658  
Order number 00032081



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

