

## LINEA

5940XSC125P30-13 RAL9002

EAN 4031582352504



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●●●

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●●○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Linea
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	130 kg
Električni provod	✓
nerdjajuci	✓
Statički Nosivost	260 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	143 mm
Ukupna širina	82 mm

## TOCAK

Materijal za telo	poliamid električna provodljivost
materijal omotaca	Poliuretan, liveno, električno provodljiv
Nošenje	precizini kuglicni lezaj, nerdjajuci
Boja omotac	Slat siva (RAL7015)
Boja Tocak	Slat siva (RAL7015)
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	20 mm
Širina tela	20 mm
Teškoća gazećeg omotac (A)	92 Šor A

## KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	precizini kuglicni lezaj
Boja	Siva bela (RAL9002)
ofset	40 mm
okretni radijus	109 mm
Otpor okretanju	218 mm
Prečnik kupole	52 mm

## PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

# LINEA

5940XSC125P30-13 RAL9002

EAN 4031582352504



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---



Deutscher  
dizajner  
Club



Interzum  
nagrada



IF nagrada za  
Dizajn