

# DELTA TWIN

9940ITP200P63

EAN 4031582365689  
Order number 00837785



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Delta twin                    |
| Housing type                | Swivel castor                 |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 750 kg                        |
| Load capacity at 6 km/h     | 600 kg                        |
| Load capacity Static        | 1500 kg                       |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 250 mm                        |
| Overall width               | 157 mm                        |
| Overall weight              | 6.172 kg                      |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Aluminium              |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | Without threadguard    |
| Diameter              | 200 mm                 |
| Tread width           | 50 mm                  |
| Body width            | 50 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material            | Iron forged, heavy     |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Colour              | Transparent coating    |
| Offset              | 55 mm                  |
| Swivel radius       | 161.5 mm               |
| Swivel interference | 323 mm                 |
| Dome diameter       | 136 mm                 |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 137 mm            |
| Plate width                 | 105 mm            |
| Plate hole length (Minimum) | 75 mm             |
| Plate hole length (Maximum) | 80 mm             |
| Plate hole width (Minimum)  | 105 mm            |
| Plate hole width (Maximum)  | 105 mm            |
| Plate hole diameter         | 11 mm             |

# DELTATWIN

9940ITP200P63

EAN 4031582365689  
Order number 00837785



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

