

MAXTECH

PNP200X30-Ø8 HL60 GRIS

EAN 4031582452785



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	30 mm
Axle hole diameter	8 mm
Hub length	60 mm
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.4 kg

MAXTECH

PNP200X30-Ø8 HL60 GRIS

EAN 4031582452785



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

