

# DURATECH HEAT

IOG 100X35-Ø8,4 CLIP

EAN 4031582347234  
Order number 00034267



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Duratech heat
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Load capacity Static	551.16 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.75 lb

## WHEEL

Body material	Aluminum
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Body width	1.38 in
Hardness of tread (D)	95 Shore D

## HOUSING

Stainless	✓
-----------	---

# DURATECH HEAT

IOG 100X35-Ø8,4 CLIP

EAN 4031582347234  
Order number 00034267



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

