

DURATECH HEAT

IOG 100X35-Ø8,4 CLIP

EAN 4031582347234
Order number 00034267



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminum
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Body width	1.38 in
Hardness of tread (D)	95 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Stainless	✓
Load capacity Static	551.16 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.75 lb

DURATECH HEAT

IOG 100X35-Ø8,4 CLIP

EAN 4031582347234
Order number 00034267



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

