PRODUCT INFORMATION

DURATECH

MOP 250x80-Ø50 HL90

EAN 4031582320084



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●○○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	6600 kg
Load capacity at 6 km/h	5500 kg
Electric Conductive	No
Stainless	No
Load capacity Static	11000 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	6.2 kg

WHEEL

Body material	Polyamide, super heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	250 mm
Tread width	80 mm
Axle Hole Diameter	50 mm
Hub Length	90 mm
Body width	80 mm
Hardness of tread (D)	75 Shore D
Bearing type	6310

© Copyright 2026 TENTE International GmbH


DURATECH

MOP 250x80-Ø50 HL90

EAN 4031582320084

Order number 00830850

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

MOP 250x80-Ø50 HL90

EAN 4031582320084

Order number 00830860



BETTER MOBILITY. BETTER LIFE.

© Copyright 2026 TENTE International GmbH