PRODUCT INFORMATION

EXPANDER

R07-Ø21,5-24 Inox_TBE

EAN 4031582437829



Image may differ from the original product

PERFORMANCE

Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Expander
Type	Accessory
Electric conductive	no
Stainless	Yes
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall weight	0.28 lb

FITTING

Fitting type	Synthetic expander, round
Expander fitting (Minimum)	0.85 in
Expander fitting (Maximum)	0.94 in
Hint	Please indicate required tube innerdiameter when ordering.

© Copyright 2026 TENTE International GmbH