

# FOOTMASTER

FOOT MASTER GD-120-S-NYN-CAL

EAN 4031582413274



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel caster
Load capacity at 1.8 mph	2204.62 lb
Electric conductive	no
Stainless	no
Load capacity Static	2204.62 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	4.72 in
Overall width	3.94 in
Overall weight	3.97 lb

## HOUSING

Housing Color	White
Offset	2.05 in
Swivel radius	3.5 in
Swivel interference	7.01 in
Dome diameter	3.94 in

## WHEEL

Bearing	Roller bearing, damped
Wheel color	Black
Diameter	2.95 in
Tread width	1.2 in
Body width	1.2 in

## FITTING

Bolt hole diameter	0.63 in
--------------------	---------

# FOOTMASTER

FOOT MASTER GD-120-S-NYN-CAL

EAN 4031582413274

Order number 00062073  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

