

GALEA

5070PJH125P30-12

EAN 4031582378641
Order number 00770899



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Galea |
| Type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 162 mm |
| Overall width | 66 mm |
| Overall weight | 0.504 kg |

WHEEL

| | |
|-----------------------|----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 30 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|----------------|
| Material fork | Polyamide |
| Fork shape | Closed |
| Swivel bearing | Two ball races |
| Offset | 40 mm |
| Swivel radius | 102.5 mm |
| Swivel interference | 205 mm |
| Dome diameter | 59 mm |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 12 mm |

GALEA

5070PJH125P30-12

EAN 4031582378641
Order number 00770899



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

