

ELASTECH HEAT

IDG 100x35 yellow HL45,5 asm.

EAN 4031582347203



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOČAK

Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Vlažnost, otpornost na visoke temperature
Nošenje	grm sa suvim ležajem
Boja Tocak	Metalni
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
dimenzija rupa osovina	8 mm
dužina glavčine	45.5 mm
Širina tela	35 mm
Teškoća gazećeg omotac (A)	75 Šor A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech heat
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	80 kg
Električni provod	no
nerdjajući	yes
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-30 °C
Opseg temperature (maksimalni)	250 °C
Ukupna težina	0.54 kg

ELASTECH HEAT

IDG 100x35 yellow HL45,5 asm.

EAN 4031582347203

Broj porudžbine 00033962
Product Drawings



BETTER MOBILITY. BETTER LIFE.

