

NOVATECH

ETP075X50-Ø25 HL50

EAN 4031582340136



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	2.95 in
Tread width	1.97 in
Axle hole diameter	0.98 in
Hub length	1.97 in
Hardness of tread (A)	92 Shore A
Bearing type	6005

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Load capacity at 1.8 mph	1212.54 lb
Load capacity Static	2425.08 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F

TECHNICAL DRAWINGS

