PRODUCT INFORMATION

# MAXTECH

## PNR260x75-Ø25 HL74 TFR

EAN 4031582400335



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Body material | Polypropylene |
| Tread material | Polyurethane, foamed |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 10.24 in |
| Tread width | 2.95 in |
| Axle hole diameter | 0.98 in |
| Hub length | 2.91 in |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement noise | ●●●○○ |
| Attrition | ●●●○○ |
| Corrosion resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product name | Maxtech |
| Type | Wheel |
| Load capacity at 1.8 mph | 165.35 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 330.69 lb |
| Overall weight | 4.3 lb |

© Copyright 2026 TENTE International GmbH


# MAXTECH

PNR260x75-Ø25 HL74 TFR

EAN 4031582400335

BETTER MOBILITY. BETTER LIFE.

## Product Drawings




© Copyright 2026 TENTE International GmbH