

PRODUCT INFORMATION

PURETECH

DIK 100x32-Ø8,1

EAN 4031582070156



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 1.26 in |
| Axle hole diameter | 0.31 in |
| Hub length | 1.42 in |
| Body width | 1.26 in |
| Hardness of tread (A) | 80 Shore A |

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Puretech |
| Type | Wheel |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 176.37 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 185 °F |
| Overall weight | 0.98 lb |

PURETECH

DIK 100x32-Ø8,1

EAN 4031582070156

Order number 00000161
Product Drawings



BETTER MOBILITY. BETTER LIFE.

