

DURATECH

TOP 080x60-Ø20 HL60

EAN 4031582365436



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	60 mm
dimenzija rupa osovina	20 mm
dužina glavnice	60 mm
Širina tela	60 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	600 kg
Nosivost na 6 km/h	500 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.44 kg

DURATECH


TOP 080x60-Ø20 HL60

EAN 4031582365436

Broj porudžbine 00860864
Product Drawings



BETTER MOBILITY. BETTER LIFE.




DURATECH

TOP 080x60-Ø20 HL60

EAN 4031582355436

Broj porudžbine 00800864



BETTER MOBILITY. BETTER LIFE.